YJ-DG3210 Mobile

Analog Radiography System



Features

 \diamond Lovely appearance, and easy to move and operate; Possess all the features of all the mobile X-ray photography machines.

 \diamond The piller can be rotated right and left $\pm 90^{\circ}$, which can easy to operate in the wards. \diamond We incorporate the latest compact high-frequency and high-voltage X-ray generator, which ensure superior image quality, while the skin dose is low, to protect the patient better.

 \diamond Adopt the technology of kV and mAs numeral closed loop control, Real-time control of the microprocessor, which ensure the accuracy and repeatability of the output dose.

 \diamond The parameter can be adjust by the KV and mAs two-button system. Highbrightness, blue screen LCD display. With multiple security protect function such as over-voltage, over-current.

 \diamond With a high-quality knockdown X-ray generator to reduce irradiation, which is

much safer to environment and operator.



