



Personal Health Care Brochure

个护保健产品册

宁波洛孚医疗科技有限公司
Ningbo Albert Novosino Co.,Ltd.

COMPANY PROFILE

公司简介

Ningbo Albert Novosino Co.,Ltd. is a high-tech medical and electronic company, including R&D, manufacturing, marketing and retailing. Former company was Germany Albert Group Sole-investment enterprise. Albert Novosino has 450 employees, including two R&D centers located in Ningbo and Shenzhen. We have over 100 patents and over 50 FDA registered products. Albert Novosino is the market leader in several niche markets.

Product lines including Class I and Class II medical devices and supplies, Personal healthcare, intelligent products. Main products including pressure infusion bag, blood pressure cuff, enema series, ENT series, massage series, sterilization and disinfection series, etc..

Processes including SMT, mold design and assembling, rotation molding, dipping molding, injection molding, CNC, 8-color printing, etc.. With molding development center, electronic hardware and software development center. Certifications including ISO13485:2016, ISO9001:2015, BSCI, CE, FDA, EMC/FCC, ROHS, etc..

Customers spreading around North America, Europe, Japan, Australia, South America, South-East Asia, Middle East, including famous customers as CVS, Walgreens, Walmart, Medline, etc..

宁波洛孚医疗科技有限公司是一家集自主研发、生产、销售为一体的国家级高新技术企业,前身是德国ALBERT集团在中国的独资企业。公司目前员工450余人,在宁波本部和深圳各拥有一处产品研发中心,拥有发明及实用新型专利超过100项,美国FDA医疗注册产品50多项。产品在多个细分市场处于行业领导地位。

公司主要产品涵盖第一、二类医疗器械,个人护理及家庭健康智能化产品等领域,产品系列涉及医用输血输液加压系列,血压监护袖带系列,灌肠护理妇科冲洗系列,耳鼻喉健康护理系列,康复按摩舒缓系列,清洁杀菌消毒系列等产品。


公司拥有电子SMT、模具开发、注塑、滚塑、浸塑、五金CNC、8色自动化印刷等一体化生产工艺,拥有自己独立的模具设计开发中心和医疗电子软硬件开发中心。公司已通过ISO13485:2016, ISO9001:2015, BSCI认证等体系认证,同时2019年通过了美国FDA官方的驻厂审核。产品已获得欧盟CE、美国FDA、EMC/FCC、ROHS等认证证书及医疗器械生产许可证、医疗器械产品注册证。

公司产品畅销北美、欧盟、日本、东南亚、澳洲、中东等地区20多个国家,主要客户有CVS, WALGREENS, WALMART, MEDLINE等大型渠道商,洛孚医疗科技一直专注于医疗家庭健康领域,致力于行业创新,以满足全球家庭健康的需求!

洛孚医疗科技,视品质为生命,我们是您值得信赖的合作伙伴!

GROUP DISTRIBUTION

集团分布



PRODUCTION WORKSHOP



生产车间



CERTIFICATION

认证

ISO13485: 2016, ISO9001: 2015
 FDA,CE,SEDEX,MDSAP
 REACH,ROHS,EMC,FCC
 BPA,PCB,PAHS,Phthalate free





Ear Irrigation Kit (ED800)

脉冲洗耳器 (ED800)

This product is mainly used for ear canal cleaning and prevention of ear canal blockage caused by cerumen.

该产品主要用于耳道清洁，预防因耳部耵聍导致的耳道堵塞问题。

- Two-level pulse design
- Low noise <58dB
- Splash-proof earmuff, one-handed operation
- Replaceable tips
- 两档脉冲功能
- 轻噪低音，低于58dB
- 防溅水耳罩，可单手操作
- 可替换喷头

Product Specifications:

Material	ABS	Input voltage	DC 5V
Product size	120x70x230mm	Rated voltage	3.7V
Weight	400g	Rated power	3.5W
Volume	200ml	Charging time	4h
Frequency	20Hz	Using time	5h
Motor speed	8000r/min	Battery capacity	2000mAh
Water flow	400ml/min	Power supply	Lithium battery (Built-in)

Ear Irrigation Kit (ED816)

脉冲洗耳器 (ED816)

This product is mainly used for ear canal cleaning and prevention of ear canal blockage caused by cerumen.

该产品主要用于耳道清洁，预防因耳部耵聍导致的耳道堵塞问题。

- Three-level pulse design
- Impact force is safe and reliable
- Portable and foldable
- Replaceable tips
- 三档脉冲功能
- 冲击力安全可靠
- 体积小，可折叠
- 可替换喷头

Product Specifications:

Material	ABS	Input voltage	DC 5V
Product size	63x50x242mm	Rated voltage	3.7V
Weight	245g	Rated power	3.5W
Volume	200ml	Charging time	2h
Frequency	20Hz	Using time	2h
Motor speed	7000r/min	Battery capacity	1200mAh
Water flow	400ml/min	Power supply	Lithium battery (Built-in)



Ear Irrigation Kit (ED826) New

脉冲洗耳器 (ED826)

This product is mainly used for ear canal cleaning and prevention of ear canal blockage caused by cerumen.

该产品主要用于耳道清洁，预防因耳部耵聍导致的耳道堵塞问题。

- Three-level pulse design
- Impact force is safe and reliable
- Portable and fold-able
- Intelligent temperature detection
- Intelligent ultraviolet sterilization
- 三档脉冲功能
- 冲击力安全可靠
- 体积小，可折叠
- 智能温度检测
- 智能紫外消毒



Product Specifications:

Material	ABS	Input voltage	DC 5V
Product size	154x58x58mm	Rated voltage	3.7V
Weight	400g	Rated power	3.5W
Volume	240ml	Waterproof level	IPX7
Motor speed	7000r/min	Battery capacity	800mAh
Water flow	400ml/min	Power supply	Lithium battery (Built-in)



Fold-able Ear Wash Basin New

可折叠洗耳盆

This product is mainly used for collect used water while ear irrigation.

该产品主要用于耳朵冲洗时回收废水。

- Unique shape, fit the ear perfectly
- Portable and fold-able
- 独特的设计更加贴合耳部轮廓
- 体积小,可折叠,方便携带



Product Specifications:

Material	PP+TPU	Product size	154x58x58mm
Volume	250ml	Product size(fold)	103x79x35mm

Ear Dryer (HE900)

耳朵烘干器 (HE900)



Prevent bacterial ear infections by drying your ears with warm, soothing air.

用温暖舒缓的空气干燥耳朵，防止细菌性耳部感染。

- 50s rapid warming
- 4-5mins rapid drying ear canal
- Patented inner circulation design of air outlet nozzle
- Keep your ear canal clean
- 50s快速升温
- 4-5分钟快速干燥耳道
- 专利出风嘴内循环设计
- 按摩清洁耳道，保持耳道干净

Product Specifications:

Material	ABS	Rated voltage	3.7V
Product size	75x63x175mm	Charging time	3.5h
Weight	135g	Battery capacity	1200mAh
Working temperature	40±2°C	Power supply	Lithium battery (Built-in)

Ear Dryer (HE901A)

耳朵烘干器 (HE901A)


Prevent bacterial ear infections by drying your ears with warm, soothing air.

用温暖舒缓的空气干燥耳朵，防止细菌性耳部感染。

- Double mode suitable in winter and summer
- 30s rapid warming
- 3-4mins rapid drying ear canal
- Patented inner circulation design of air outlet nozzle
- Keep your ear canal clean
- 冬夏双模式
- 30s极速升温
- 3-4分钟快速干燥耳道
- 专利出风嘴内循环设计
- 按摩清洁耳道，保持耳道干净

Product Specifications:

Material	ABS	Rated voltage	3.7V
Product size	82x67x171mm	Charging time	3.5h
Weight	140g	Battery capacity	1200mAh
Working temperature	40-45°C	Power supply	Lithium battery (Built-in)





Ear Dryer (HE901B)

耳朵烘干器 (HE901B)

Prevent bacterial ear infections by drying your ears with warm, soothing air.

用温暖舒缓的空气干燥耳朵，防止细菌性耳部感染。

- Double mode suitable in winter and summer
- 30s rapid warming
- 3-4mins rapid drying ear canal
- Patented inner circulation design of air outlet nozzle
- 650nm red light physiotherapy
- 冬夏双模式
- 30s极速升温
- 3-4分钟极速烘干耳道
- 专利出风嘴内循环设计
- 650纳米红光理疗

Product Specifications:

Material	ABS	Rated voltage	3.7V
Product size	82x67x171mm	Charging time	3.5h
Weight	140g	Battery capacity	1200mAh
Working temperature	40-45°C	Power supply	Lithium battery (Built-in)

Ear Dryer (HE902)

耳朵烘干器 (HE902)

Prevent bacterial ear infections by drying your ears with warm, soothing air.

用温暖舒缓的空气干燥耳朵，防止细菌性耳部感染。

- Two gear option
- NTC Intelligent temperature control
- Low noise, <45dB
- 30s rapid warming
- 2-3mins rapid drying ear canal
- Patented inner circulation design of air outlet nozzle
- 650nm red light physiotherapy
- Pocket Portable
- 两档可选
- NTC智能控温
- 轻噪低音，小于45dB
- 30s极速升温
- 2-3分钟极速烘干耳道
- 专利出风嘴内循环设计
- 650纳米红光理疗
- 口袋式便携

Product Specifications:

Material	ABS	Rated voltage	3.7V
Product size	61x36x125mm	Charging time	1.5h
Weight	75g	Battery capacity	700mAh
Working temperature	38°C/40°C	Power supply	Lithium battery (Built-in)



Ear Dryer (HE903)



耳朵烘干器(HE903)

Prevent bacterial ear infections by drying your ears with warm, soothing air.

用温暖舒缓的空气干燥耳朵，防止细菌性耳部感染。

- Three gears options of Temperature
- Digital display screen Temperature
- Two gears options of air blower
- NTC Intelligent temperature control
- Low noise, <45dB
- Patented inner circulation design of air outlet nozzle
- 650nm red light physiotherapy
- 三挡温度可选
- 数码显示温度
- 两档风速循环
- NTC智能恒温控制
- 2-3分钟极速烘干耳道
- 专利出风嘴内循环设计
- 650纳米红光理疗



Product Specifications:

Material	ABS	Rated voltage	3.7V
Product size	39.4x151.7x82.4mm	Charging time	1.5h
Weight	100g	Battery capacity	700mAh
Working temperature	38°C/40°C/42°C	Power supply	Lithium battery (Built-in)



Ear Dryer (HE907)

耳朵烘干器(HE907)

Prevent bacterial ear infections by drying your ears with warm, soothing air.

用温暖舒缓的空气干燥耳朵，防止细菌性耳部感染。

- Two gear option
- NTC Intelligent temperature control
- Low noise, <45dB
- 30s rapid warming
- 2-3mins rapid drying ear canal
- Patented inner circulation design of air outlet nozzle
- 650nm red light physiotherapy
- Pocket Portable
- 两档可选
- NTC智能控温
- 轻噪低音, 小于45dB
- 30s极速升温
- 2-3分钟极速烘干耳道
- 专利出风嘴内循环设计
- 650纳米红光理疗
- 口袋式便携

Product Specifications:

Material	ABS	Rated voltage	3.7V
Product size	65x46x130mm	Charging time	1.5h
Weight	92g	Battery capacity	700mAh
Working temperature	38°C/40°C	Power supply	Lithium battery (Built-in)

Otoscope (OS801)

可视化采耳棒(OS801)

APP connection is visualized and clean ear collection to realize ear health home self-examination.

APP连接可视化清洁采耳，实现耳部健康居家自检。

- Open the cover and start the machine
- WiFi real-time video
- Hd camera
- Ear health home self-examination
- Two safety cones (adult,child)
- 开盖即开机
- 无线WiFi实时影像
- 高清摄像头
- 耳部健康居家自检
- 两款安全锥(成人,儿童)



Product Specifications:

Material	AL	Pixel	1000W
Product size	Φ13.6x135mm	Best focus	1.5-2cm
Input voltage	DC 5V	Lamp beads	6 pieces
Charging time	1.5h	Gyroscope	4 axis
Battery capacity	350mAh	Camera diameter	3.9mm
Working Environment	-10°C-50°C	App connection	IOS/Android


Otoscope (OS806)

可视化采耳棒 (OS806)

APP connection is visualized and clean ear collection to realize ear health home self-examination.

APP连接可视化清洁采耳，实现耳部健康居家自检。

- Open the cover and start the machine
- WiFi real-time video
- Hd camera
- Ear health home self-examination
- Two safety cones (adult,child)
- 开盖即开机
- 无线WiFi实时影像
- 高清摄像头
- 耳部健康居家自检
- 两款安全锥(成人,儿童)



Product Specifications:

Material	AL	Pixel	1000W
Product size	Φ13.6x135mm	Best focus	1.5-2cm
Input voltage	DC 5V	Lamp beads	6 pieces
Charging time	1.5h	Gyroscope	4 axis
Battery capacity	350mAh	Camera diameter	3.9mm
Working Environment	-10°C-50°C	App connection	IOS/Android

Otoscope (OS811)

可视化采耳棒 (OS811)

APP connection is visualized and clean ear collection to realize ear health home self-examination.

APP连接可视化清洁采耳，实现耳部健康居家自检。

- WiFi real-time video
- Integrated earpick design
- Hd camera
- 无线WiFi实时影像
- 一体式耳勺设计
- 高清摄像头



Product Specifications:

Material	ABS	Pixel	1000W
Product size	Φ14x141mm	Best focus	1.5-2cm
Input voltage	DC 5V	Number of lights	6 pieces
Charging time	1h	Gyroscope	4 axis
Battery capacity	150mAh	Camera diameter	3.6mm
Working Environment	-10°C-50°C	App connection	IOS/Android



Otoscope (OS821)

可视化采耳棒 (OS821)

APP connection is visualized and clean ear collection to realize ear health home self-examination.

APP连接可视化清洁采耳，实现耳部健康居家自检。

- WiFi real-time video
- Hd camera
- Ear health home self-examination
- Two safety cones (adult,child)
- Integrated ear-spoon storage bin
- 无线WiFi实时影像
- 高清摄像头
- 耳部健康居家自检
- 两款安全锥(成人,儿童)
- 一体耳勺收纳仓



Product Specifications:

Material	ABS	Pixel	1000W
Product size	Φ14x145mm	Best focus	1.5-2cm
Input voltage	DC 5V	Lamp beads	6 pieces
Charging time	1.5h	Gyroscope	4 axis
Battery capacity	350mAh	Camera diameter	3.9mm
Working Environment	-10°C-50°C	App connection	IOS/Android

Ear Massager for Stress Relief (SR822)

解压采耳器 (SR822)

This product is mainly used for ear canal cleaning and by massaging to soothe and destress.

该产品主要用于耳道清洁，通过按摩起到舒缓减压的作用。

- Two gear option
- Three soothing music
- Four kinds of massage accessories
- Low noise < 45dB
- Natural animal feather
- Pocket Portable
- 两档可选
- 三种舒缓白噪音
- 四种按摩配件
- 轻噪低音，小于45dB
- 天然动物羽毛
- 口袋式便携



Product Specifications:

Material	ABS	Weight	75g
Product size	Φ30x125mm	Battery capacity	600mAh
Input voltage	DC 5V	Working power	0.5w
Charging time	1.5h	Operating voltage	3.7V

Headphone Cleaning Kit

清洁套装

The dust-removing brush cleans the stains in the gap, suitable for dust and impurities in the gap of the headphone slot, keyboard lens, etc., and easily cleans all corners.

Dedusting prevents ear infections.

除尘刷清洁间隙中的污渍，适用于耳机槽，键盘镜头等缝隙中的灰尘杂质，轻松清洁各个角落。

除尘后可预防耳朵感染。



Ear Pain Relief (ER812)

耳鸣按摩仪 (ER812)



Cause eustachian tube vibration through bone transmission, so that the inflammatory substances in the eustachian tube can be discharged as soon as possible, safe and painless.

通过骨传输引起咽鼓管振动,使咽鼓管内的炎性物质能尽快排出,安全无痛。

- Multi-frequency massage
- Crescent head design, fitting ear
- 6 levels vibration adjustment
- Physical relief, no side effect
- 多频按摩
- 月牙头设计, 贴合耳部
- 6档震动调节
- 物理缓解, 无副作用

Product Specifications:

Material	ABS	Input voltage	DC 5V
Product size	45x42x191mm	Charging time	2h
Weight	120g	Using time	15h
Vibration frequency	15-32Hz	Battery capacity	1200mAh
Power supply	Lithium battery (Built-in)		

Ear Pressure Relief (ER813)

中耳负压调节仪 (ER813)

Air is delivered to the eustachian tube to ventilate the middle ear to relieve the negative pressure of the middle ear and drain the middle ear fluid to restore hearing.

将空气输送至咽鼓管,使中耳通气,减轻中耳负压,排出中耳液,恢复听力。

- Multi-frequency massage
- Air supply mode
- Two mode optional (adult, child)
- Single side plug hole design, can be operated with one hand
- The left and right nostril can be switched
- 6 levels vibration adjustment
- Physical relief, no side effects
- Double detachable design, easy to clean
- 多频按摩+供气模式
- 双模式可选(成人, 儿童)
- 单边堵孔设计, 可单手操作
- 左右鼻孔可切换使用
- 6档震动调节
- 物理缓解, 无副作用
- 双头可拆卸设计, 清洗方便

Product Specifications:

Material	ABS	Input voltage	DC 5V
Product size	45x42x192mm	Charging time	1.5h
Weight	155g	Using time	3h
Air pressure	20-40Kpa	Battery capacity	800mAh
Vibration frequency	15-32Hz	Power supply	Lithium battery (Built-in)



ER813A

ER813B

Bluetooth Hearing Aid (HA818)

蓝牙助听器 (HA818)

There are no effective drugs and surgical methods to treat the hearing impairment of most elderly people, and hearing aids are generally required. Hearing aids to cope with everyday life.

多数老年人的听力障碍问题，目前还没有特效的药物和手术手段可以治疗，一般需佩戴助听、辅听设备。

- 12 channels for left and right ears
- out-of-the-box
- Intelligent compensation for hearing loss
- Hearing aid, call, music manual switch
- Rejecting the sound of whistling
- Super long standby 16 hours
- Hanging neck not easy to fall off
- 左右耳12通道
- 即开即用
- 听损智能补偿
- 助听、通话、音乐手动切换
- 不易啸叫
- 超长待机16小时
- 挂脖不易掉

Product Specifications:

Input voltage	DC 3.7V	Bluetooth version	V5.2
Charging current	200mA	Bluetooth audio duration	25h
Charging time	1h	Hearing aid duration	28h
Battery capacity	200mAh	Charging method	TYPE-C



Bluetooth Hearing Aid (HA819)

蓝牙辅听器 (HA819)

There are no effective drugs and surgical methods to treat the hearing impairment of most elderly people, and hearing aids are generally required. Hearing aids to cope with everyday life.

多数老年人的听力障碍问题，目前还没有特效的药物和手术手段可以治疗，一般需佩戴助听、辅听设备。

- 24 channels for left and right ears
- App self-test and match
- Intelligent compensation for hearing loss
- Smart noise reduction
- Automatic music switching between hearing aid calls
- Hanging neck not easy to fall off
- 左右耳12通道
- App自主验配
- 听损智能补偿
- 智能降噪
- 助听通话音乐自动切换
- 挂脖不易掉

Product Specifications:

Input voltage	5V	Bluetooth version	V5.2
Charging current	200mA	Bluetooth audio duration	25h
Charging time	1.5h	Hearing aid duration	28h
Battery capacity	250mAh	Charging method	TYPE-C



Ear Irrigation Kit

喷枪式洗耳器

The skin in the ear is very sensitive and needs special care. Our ear-washing kit can gently rinse your ears without damaging the skin and is the best choice for removing earwax and other harmful substances.

耳内皮肤非常敏感,需要特别护理。我们的洗耳清洁包能够温和的冲洗您的耳朵,不损害皮肤,是去除耳垢和其他有害物质的最佳选择。



C0301016



C0301014



C0301107



C0301121



C0302001



C0301128



C0301127



C0301133



C0301128

Accessories list

配件清单:



Double ear scoop



Stainless steel ear scoop



Spiral ear scoop



Luminous ear scoop



Electric ear scoop



Cleaning the ear stick

Product Superiority

We are equipped with the finest computerized rotational molding equipment and manufacture rotational and injection-molded elastomer products for medical and technical usage. Our computerized precision equipment ensures a consistency of quality and workmanship that is second to none. This means our products are made of one-piece constructions without bonded seams to come apart or imperfect surfaces. Ear syringes can be used for a variety of cleansing and suction applications.

我们配备了最好的计算机设备，并制造用于医疗和技术用途的滚塑和注塑产品。我们的计算机化精密设备确保了首屈一指的质量和工艺的一致性。这意味着我们的产品是一体式结构，没有粘结接缝，不会破裂，也没有不完美的表面。洗耳球可以用于各种清洁和抽吸应用。

Medical Grade Ear Bulb Syringes

Ear syringes can be used for a variety of cleansing and suction applications. They can also be used for any aspiration or irrigation procedure. Our bulbs are made from medical-grade and are not made with BPA, phthalates or latex. Our products are also made in one piece using the rotational molding process so that there are no bonded seams, which could fail during service or foster bacterial buildup.

洗耳球可用于各种清洁和抽吸应用。它们还可用于任何抽吸或灌洗应用。我们的洗耳球由医用级材质制成，不含双酚A、邻苯二甲酸盐或乳胶。另外，我们的产品是采用滚塑成型工艺制成的，因此没有粘合的接缝，更便于清洁和使用。

Ear Syringe Bulb

洗耳球



Specification List

Item	Volume	L (mm)	D1 (mm)	Bulb	Surface
1	15ml	65	37.5	○	Mat
2	27ml	87	44	○	Mat
3	41ml	95	47	○	Mat
4	65ml	104	54	○	Mat
5	75ml	115	57	○	Mat
6	90ml	126	62	○	Mat
7	135ml	138	71	○	Mat
8	206ml	148	83	○	Mat
9	317ml	173	93	○	Mat

Item	Volume	L (mm)	D1 (mm)	Bulb	Surface
1	25ml	85	41	○	Shiny with rings
2	65ml	104	54	○	Shiny with rings
3	90ml	126	62	○	Shiny with rings

Ningbo Albert Novosino Co.,LTD

Address: No.1206 Qingfeng West Road, Sanqishi
Town, Yuyao City, Zhejiang Province,
315412, P.R. China

宁波洛孚医疗科技有限公司

单位地址: 浙江省余姚市三七市镇庆丰西路1206号

联系电话: 0574-87527883

传 真: 0574-87527880

公司网址: www.albertnovosino.com



<http://www.albertnovosino.com>