


SE902 

TABLE II (continued)

			Selection	5	6
Special Purpose	621-0021RC	Enhanced Diagnostics Module	J	•	•
	621-1002RC	3 Asyn Port MiniCOP Module (Note 3)	U	•	•
Digital	621-1160R	115 Vac Digital Input, 16 pts.	K	•	•
	621-3560RC	24 Vdc Digital Input, 16 pts.	L	•	•
	621-2150RC	115 Vac Digital Output, 16 pts.	M	•	•
	621-6550RC	24 Vdc Digital Output, 16 pts.	N	•	•
	621-2101RC	115 Vac Isolated Digital Output, 6 pts.	P	•	•
	621-1100RC	115 Vac Digital Input, 8 pts.	Q	•	•
	621-1101RC	115 Vac Isolated Digital Input, 6 pts.	R	•	•
	621-2100RC	115 Vac Digital Output, 8 pts.	S	•	•
	621-3580RC	24 Vdc Digital Input, 32 pts.	T	•	•
	621-6575RC	24 Vdc Digital Output, 32 pts.	V	•	•

TABLE III

Cables	Remote Installation (user supplied cable) Note 4)	0	•	•
	Vertical Installation (9" cable)	1	•	•
	Horizontal Side by Side Installation (48" cable)	2	•	•
	Diagonal Installation (72" cable)	3	•	•

NOTE 1: Denotes a slot for other I/O modules not listed here.

NOTE 2: Includes 8 precision resistors - see Spare Parts List for additional resistors.

NOTE 3: Occupies two slots, must be preceded by a Y (empty slot).

NOTE 4: If None is selected for SE9025, you must add a separate line item for the parallel I/O cable

Available Support Services

Software Enhancement and Support Plan Contact Regional Business Center

Implementation Support Services Contact Regional Business Center